framatome

KOPRA - Test Section for Control Rod Drive Mechanisms

Dedicated test facility for CRDMs used in PWRs

Factory acceptance tests for all types of CRDMs used in PWRs

Challenge

Factory Acceptance Tests (FAT) of core components such as the CRDM (Control Rod Drive Mechanism) are crucial steps in manufacturing processes. They prove that the component fulfills all the functional requirements. The tests must be supported by a suitable test facility, as well as by experienced and qualified staff. This high level of quality is also required for research, developments and qualification activities.

Solution

Framatome operate the KOPRA CRDM Test Section, which is designed for qualification tests of CRDM under operational conditions in order to fulfill all possible testing requirements. It consists of three test sections, a closed loop with circulation pump, heating and cooling systems, and a pressurizer.

The CRDMs are mounted on flanges on top of the test sections, and inside the drive rods are connected to dummy weights simulating the Rod Cluster Control Assembly (RCC-A) weights.

For testing, the flow circuit heats the CRDMs up to operating temperature. Stepping operation for the overall travel length and drops from the uppermost position are possible. At the end of the drop, a hydraulic damper slows the dummy weight.

The CRDM test sections can be adapted to all CRDM types used in PWRs.

The test facility can also be adapted to test other components that need to be tested at PWR conditions regarding pressure and temperature. Even the special water chemistry requirements can be set (oxygen content, conductivity, boron content).

Customer benefits

- Relevant test results with tests performed at operational conditions
- Flexibility in testing different CRDM design and control systems
- Benefit from experienced personnel and comprehensive test laboratory
- Reliable test results through accreditation as test and inspection body in accordance with ISO 17025 and 17020, accepted by ILAC



Set-up for CRDM factory acceptance test

Your performance is our everyday commitment

Technical information

A typical FAT for CRDM testing is performed as follows:

After manufacturing and assembly, every CRDM must be qualified under operational conditions. The first functional test phase under operational conditions generates a magnetite layer on the sliding surfaces of the latch unit components, ensuring optimal antifriction properties. This is the basic requirement for dependable CRDM latch unit functionality.

The factory acceptance test ensures the three operational functions of the CRDM:

- Insertion and withdrawal of the mobile set (drive rod with coupled Rod Cluster Control Assembly dummy weight) in single steps to the required operating position.
- Holding of the mobile set at any selected position along the travel length.
- Releasing of the mobile set (for reactor trip).

In addition, qualification can be performed of the complete CRDM as part of special investigations for new designs, e.g. a rod position indicator system.

For CRDM operation, various generations of PWR rod control systems are available, (such as contactor control, ELSTABE, RodPilot® 10 and 40).



Set-up for CRDM factory acceptance test

Key figures

20 to 330°C and 10 to 160 bar

in 3 test sections



Components of the CRDM



RodPilot® 10 control cabinet

Contact: test-labs@framatome.com

www.framatome.com

It is prohibited to reproduce the present publication in its entirety or partially in whatever form without prior written consent. Legal action may be taken against any infringer and/or any person breaching the aforementioned prohibitions.

Subject to change without notice, errors excepted. Illustrations may differ from the original. The statements and information contained in this publication are for advertising purposes only and do not constitute an offer of contract. They shall neither be construed as a guarantee of quality or durability, nor as warranties of merchantability or fitness for a particular purpose. These statements, even if they are future-orientated, are based on information that was available to us at the date of publication. Only the terms of individual contracts shall be authoritative for type, scope and characteristics of our products and services.



10 Eramatome GmbH / PS-G-1580-ENG-2019