

FILTERED CONTAINMENT VENTING SYSTEM-FCVS STANDARD

Efficient Containment Pressure and Activity Release Limitation

Framatome's FCVS allows release of excess pressure from the containment to the environment, while its robust design and extensive qualification ensure reliable filtration and comparably low activity releases due to high decontamination factors.

Challenge

In the event of a severe accident, the pressure inside the containment may rise excessively; in such cases, the containment as the last physical barrier for enclosed radioactivity must remain intact, to prevent significant long-term off-site land contamination.

To ensure this, it is necessary to:

- Limit excessive pressure build-up in the containment;
- Limit the off-site radiological consequences to an absolute minimum;
- Safely store or return captured fission products to the containment; and
- Control decay heat removal from the capture fission products.

Solution


Framatome's Standard Filtered Containment Venting System (FCVS Standard) provides reliable depressurization of the containment while efficiently retaining the radioactive aerosols and elemental as well as organic iodine. It combines the advantages of a high-speed venturi scrubber (stage 1) with a highly efficient metal fiber filter (stage 2).

The system operates fully passive and thus does not require external power for activation or operation. The two stages are arranged inside a robust pressure vessel and ensure safe containment depressurization. During operation and depressurization, the system handles large amounts of energy released from the containment while ensuring highest fission product retention rates.

Thanks to the modular, compact design, Framatome's FCVS is easy to retrofit into existing buildings at low cost. The system can be easily adapted to any nuclear power plant type, type of containment or other design parameters without impacting the systems efficiency or qualification. Potential layout restrictions can be met by the system design dividing the sections into separate vessels (split vessel design).

Framatome's patented approach ensures high decontamination factors for iodine, large and fine aerosols in a very compact design.

The system is designed entirely as pressure equipment and provides an essential safety feature in case of postulated hydrogen deflagration.



3D model of a split vessel design of Framatome's FCVS Standard

Customer benefits

- Fulfilling regulatory requirements.
- Cost effective prevention of excessive containment pressure build up.
- High retention rates for all types of fission products, aerosols and iodine.
- Reliably retaining activity in short & long-term conditions.
- Large scale qualification Internationally accepted.
- Compact size, high flexibility by split vessel design, tailor made for customer specific plant parameters.

Technical information


Stage 1: Venturi Scrubber

The venturi scrubber is operated at a pressure close to the prevailing containment pressure. The vent gas is accelerated to high velocities in the venturi nozzles and injected into the scrubbing liquid. As it passes through the throat of the venturi nozzle, a suction is created that carries scrubbing liquid with it.

The high velocity difference ensures retention of more than 99% of the aerosols and more than 99.5% of the elemental iodine are retained due to Framatome's unique process design. During the scrubbing process, the decay heat transfers to the scrubbing liquid and does not require any active measures.

Stage 2: Metal Fiber Filter


The second stage consisting of metal fiber filters retains the hard to retain micro-aerosols and scrubbing water droplets still contained in the vented gas flow downstream of stage 1. Furthermore, the metal fiber elements capture re-suspended aerosols. Crucial for effectiveness of this stage is the removal of droplets and condensate, which is ensured by the optimized filter design. The combination of stage 1 and stage 2 provides retention rates for aerosols of more than 99.99%.



Schematic of Framatome's FCVS Standard



Example of Stage 1 Venturi Scrubber



Example of Stage 2 Metal Fiber Filter

References

Filtered Containment Venting System applications are installed in more than **100** PWR, BWR, CANDU, ABWR and PHWR reactors worldwide.


Patent rights reserved.

Licensing

Framatome has broad experience on licensing and supports utilities by an extensive qualification and large scale verification data base in the discussion with regulators.

Extensive process qualification and performance verification

- Full scale process section tests (JAVA Plus Test Facility Karlstein)
- Third party and international testing
- Tests performed with representative accident aerosols at high pressure and temperatures
- Retention tests with gaseous iodine (elemental and organic iodine)
- Seismic Qualification (up to 8 g (peak) respectively 5 g (rigid body))



**Contact: integrated-systems@framatome.com
www.framatome.com**

It is prohibited to reproduce the present publication in its entirety or partially in whatever form without prior written consent. Legal action may be taken against any infringer and/or any person breaching the aforementioned prohibitions.

Subject to change without notice, errors excepted. Illustrations may differ from the original. The statements and information contained in this publication are for advertising purposes only and do not constitute an offer of contract. They shall neither be construed as a guarantee of quality or durability, nor as warranties of merchantability or fitness for a particular purpose. All statements, even those pertaining to future events, are based on information available to us at the date of publication. Only the terms of individual contracts shall be authoritative for type, scope and characteristics of our products and services.

Your performance
is **our everyday commitment**